Eclipse Solar Suitcase

Renogy 100W | 200W w/o CC Manual





2775 E. Philadelphia St., Ontario, CA 91761 1-800-330-8678

Version 1.1



Please save these instructions.

This manual contains important safety, installation, and operating instructions for the charge controller. The following symbols are used throughout the manual to indicate potentially dangerous conditions or important safety information.

⚠ WARNING: Indicates a potentially dangerous condition. Use extreme caution when performing this task.

CAUTION: Indicates a critical procedure for safe and proper operation of the controller

NOTE: Indicates a procedure or function that is important to the safe and proper operation of the controller.

General Safety Information

- Read all of the instructions and cautions in the manual before beginning the installation.
- It is HIGHLY recommended to install a charge controller in order to charge your batteries using the solar suitcase.
- It is dangerous for unregulated panels to be connected to battery banks.

Battery Safety

- Use only sealed lead-acid, flooded, or gel batteries which must be deep cycle.
- Explosive battery gases may be present while charging. Be certain there is enough ventilation to release the gases.
- Be careful when working with large lead acid batteries. Wear eye protection and have fresh water available in case there is contact with the battery acid.

- Carefully read battery manuals before operation.
- Do NOT let the positive (+) and negative
 (-) terminals of the battery touch each other.
- Recycle battery when it is replaced.
- Over-charging and excessive gas precipitation may damage the battery plates and activate material shedding on them. Too high of an equalizing charge or too long of one may cause damage. Please carefully review the specific requirements of the battery used in the system.
- Equalization is carried out only for nonsealed / vented/ flooded / wet cell lead acid batteries
- Do NOT equalize sealed / VRLA type AGM / Gel cell batteries UNLESS permitted by battery manufacturer.

Table of Contents

General Information	. 3
Identification of Parts	
Installation	
Recommended Wiring	
Frequently Asked Questions	
Technical Specifications	
Solar Panel Parameters	
Dimensions	

General Information

The Renogy **Eclipse Solar Suitcase** is specifically designed for mobile off-grid applications, where space and weight limitations are abundant. The Solar Suitcase models support 12V deep cycle battery varieties such as sealed-lead acid, gel, and flooded. With built-in tilting stands, these panels can be adjusted at different angles to maximize the power output throughout the seasons.


The alligator clips included in this package make it easy to connect the panel to a battery in seconds. If one ever needs to connect a battery with a different type of end terminal, the alligator clips are attached via MC4 Connectors.

Key Features

- Tilting stand for maximum solar generating potential.
- Convenient storage case for easy transportation.
- High efficient monocrystalline solar panels

NOTE: The suitcase requires an adaptor kit, a charge controller, and a tray cable. These components require a separate purchase.

Identification of Parts




Key Parts


- 1. Junction Box
- 2. Tilt Stands
- 3. Latches
- 4. Handle
- 5. MC4 Connections

Installation

1. Unlatch and unfold




2. Unscrew butterfly nut tilt to desired angle and lock butterfly nut



To maximize the output, adjust the angle of the suitcase regularly to track the sun's movement throughout the season

After




Recommended Wiring

The Solar Suitcase is shipped by itself without any additional components. In order to utilize the suitcase efficiently, it is highly recommended that users put their system together with the following components:


- 1. **Adapter kit**—has an MC4 connection on one end and bare wire on the other end for connecting to a charge controller.
- 2. **Charge controller**—regulates the solar panel power to efficiently charge batteries.
- 3. **Tray cable**—has a bare wire on one end and a battery "O-ring" on the other end for connecting the charge controller to the battery bank.
- 4. **Battery bank**—where power from the solar panels will be stored.

NOTE: Depending on the user's preference, different gauge wires, wire lengths, charge controllers, and cables could possibly be used.


1. Use tray cable to connect battery bank to charge controller's battery terminals



2. Connect adapter kit to MC4 connections coming from the suitcase's junction box



3. Connect adapter kit to charge controller PV terminals



Frequently Asked Questions

Q. Can the kit charge two or more 12V batteries connected in parallel?

A. Yes, it's possible if the batteries have the same type and capacity and are wired in parallel as a single 12V battery bank.

Q. Is there any risk that the solar kit will over charge my battery?

A. One of the functions of the solar charge controller is to ensure that your battery is not over charged; therefore there is no risk of overcharge.

Q. Can I extend the battery leads?

A. Yes, it's possible – please choose the same size of cable for extension. However, there longer the extension, the greater the line loss. Bigger gauge will be required for longer runs.

Q. Do I need to clean the solar panels?

A. Yes, it is recommended for better performance. Dust and dirt should first be swept off the panel surface using a soft brush. When the sweeping is complete, use a wet cloth to wipe the panel surface to remove remaining dirt and grime.

Q. Can rain damage the solar kit?

A. The solar panels are fully waterproof (IP66 class), the controller is not. We recommend protecting the kit from rain, since water into controller may damage the internal circuitry.


Technical Specifications

Solar Panel Parameters

Description	100 W Parameters	200 W Parameters
Maximum Power	100 W	200 W
Open Circuit Voltage (Voc)	21.6 V	21.2 V
Short Circuit Current (Isc)	6.10 A	11.72 A
Maximum Power Voltage (Vmp)	17.6 V	17.7 V
Maximum Power Current (Imp)	5.68 A	10.35 A
Cell Type	Monocrystalline	Monocrystalline
Operating Temperature	−40°F to +185°F	−40°F to +185°F
Folded Size	21.1 X 21.5 X 3.1 in	41.3 X 21.1 X 3.1 in
Net Weight	19.40 lbs.	33.60 lbs.


Dimensions

100W Eclipse Suitcase



• Leg stand length: 18 in. (long part), 14.5in. (short part)

200W Eclipse Suitcase



• Leg stand length: 26.3 in. (long part), 23.3 in. (short part)

Revision: 6/1/2017